

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200740160](#)
Status: **Active**
Overview: [Brad Micro-Change \(M12\) Connectors](#)
Description: Micro-Change (1/2" - 20 UNF) US Dual Keyway Receptacle, 4 Poles, 1/2" -14 NPT Mounting Threads, Male (Straight) to 22 AWG PVC Leads, 0.305m (1.0') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Receptacles
Series [120074](#)
IP Rating IP67
NEMA Rating NEMA 6
Overview [Brad Micro-Change \(M12\) Connectors](#)
Product Name Micro-Change (1/2" - 20 UNF)
Type Single Ended (pigtail)
UPC 78678822692

Physical

Coupling Type External Thread
Gender Male
Keyway Dual
Length 0.305m
Material - Component Gray Anodized Aluminum
Mounting Thread Size 1/2" - 14 NPT
Orientation Straight
Panel Mount Front
Poles 4
Temperature Range - Operating -20° to +80°C
Wire Size AWG 22
Wire/Cable Type Leads, UL 1061

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 7R4006A19A120

Reference - Drawing Numbers

Sales Drawing SD-120074-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120074 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120074-0160](#)