


10 9 8 7 6 5 4 3 2 1



VOLTAGE RATING: 4 POLE: 250 VAC/VDC
AMPERAGE RATING: 4A
PROTECTION CLASS: IP 67
OPERATING TEMPERATURE: -25°C / 90°C
CSA CERTIFICATIONS: FILE NO. LR6837

14	1	GASKET OR	NBR (BLACK)	-
13	1	SLEEVE U12 MA STR	V4A	-
12	1	SLEEVE MA	V4A	-
11	1	SPRING U12U	V4A	-
10	1	GASKET	EPDM (BLACK)	-
9	1	GASKET	FPM (RED)	-
8	4	CONTACT MA U12 FA	BRASS	NI
7	1	INSERT U12 FA	PA (BLACK)	-
6	1	INSERT U12 4P AC	PA (BLACK)	-
5	1	LOCK RING FA	PA (BLACK)	-
4	4	SCREW FA	ST	-
3	1	ENDSLEEVE STR PG9 FA	PA (BLACK)	-
2	1	GROMMET PG9	CR/NBR (BLACK)	-
1	1	HUT NUT FA PG9	PA (BLACK)	-
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

POL	MATERIAL NO.	ENGINEERING NO.
4	1200850020	WA4006-328

ENTER DESCRIPTION EC NO: IPG2016-1096 DRWN:RSCHIEBER 2016/02/16 CHKD:REISSNER 2016/02/16 APPR:RSILLER 2016/03/01 2	DESCRIPTION QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY RSCHIEBER	DATE 2016/02/08	TITLE FA U12 4P AC MA STR PG9 BK V4A	molex	SHEET NO. 1 OF 1	
		4 PLACES	± ---	± ---	CHECKED BY	DATE				
		3 PLACES	± ---	± ---	REISSNER	2016/02/08				
		2 PLACES	± 0.05	± ---	APPROVED BY	DATE				
		1 PLACE	± 0.30	± ---	RSILLER	2016/03/01				
		0 PLACE	± 0.50	± ---	MATERIAL NO.		DOCUMENT NO.			
		ANGULAR ± 1 °		SEE TABLE		SD-120085-009				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

9 8 7 6 5 4 3 2 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200850020](#)