

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200860146](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 24 AWG, PVC Cable, 4.0m (13.12') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [120086](#)
Connector End A Nano-Change (M8)
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Nano-Change \(M8\) Products](#)
Product Name Nano-Change (M8)
Region America
Type Single Ended
UPC 78678832851

Physical

Cable Diameter 4.57mm (.180")
Cable Length 4.0m (13.12')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Pigtail
Keyway A-coded
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body TPE
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold
Net Weight 399.000/g
Orientation Straight to Pigtail
Poles 4
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 24
Wire/Cable Type UL 2661

Electrical

Current - Maximum per Contact 3.0A
Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 404000A10M040



Series image - Reference only

EU ELV

**Compliant with
Exemption 3**

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant with Exemption 3
RoHS Phthalates	Not Contained

Search Parts in this Series

[120086](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200860146