

F

E


D

C

B


A

FRONT VIEW - MALE M12




1-WHITE/ORANGE
2-WHITE/GREEN
3-ORANGE
4-GREEN

FRONT VIEW - MALE M12



1-WHITE/ORANGE
2-WHITE/GREEN
3-ORANGE
4-GREEN



NOTES:

MECHANICAL

M12 CONNECTOR

INSERT: BLACK PUR

CONTACT: GOLD/NICKEL OVER COPPER ALLOY

COUPLING NUT: NICKEL PLATED BRASS

MOLDED BODY: BLACK PUR

CABLE: 24 AWG 2 PAIR CONDUCTORS TEAL TPE JACKET

UL LISTED: CMR

CSA LISTED: CMG

WRAP LABEL: MARKED WITH P/N, DATE CODE, VOLTAGE & AMPERAGE


ELECTRICAL

ACCORDING TO CAT5e

VOLTAGE RATING: 30V AC/DC

AMPERAGE: 1.5A

ADDED PART NO. TABLE EC NO: IPG2015-2010 DRWN: GGUSTAFS 2015/05/26 CHKD: BARDEN 2015/07/23 APPR: BWOODMAN2013/06/04		DESCRIPTION REV	QUALITY SYMBOLS <div>▽=0</div> <div>▽C=0</div>	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE INCH ONLY		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION				
					mm	INCH	DRAWN BY	DATE	TITLE M12 ETHERNET CORDSET 4P MALE/MALE M12 ST/ST #24-2P TEAL TPE CAT5E						
				4 PLACES	±---	±---	BARDEN	2013/01/29							
				3 PLACES	±---	±.005	CHECKED BY	DATE							
					2 PLACES	±0.13	±.010	VOU	2013/04/26	molex MOLEX INCORPORATED					
	1 PLACE	±0.25	±.020	APPROVED BY	DATE										
	ANGULAR ±.5°			BWOODMAN 2013/06/04		SD-120108-057									
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE TABLE								DOCUMENT NO.			
	C				SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
						SHEET NO. 1 OF 2									



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1201080387