

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


1201088090

Status:

Active

Description:

Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), 26 AWG, Shielded TPE Cable, 15.0m (49.21') Length, 6.00mm (.236") Diameter, Teal



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E361772
General	
Product Family	Industrial Cordsets
Series	120108
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Performance Category	5e
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78172535944
Physical	
Cable Diameter	6.00mm (.236")
Cable Length	15.0m (49.21')
Color - Cable Jacket	Teal
Coupling Style	Threaded
Gender	Male-Male
Keyway	D-coded
LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +75°C
Wire Size AWG	26
Wire/Cable Type	Shielded TPE
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	125V
Material Info	
Engineering Number	E11A06005M150
Reference - Drawing Numbers	
Sales Drawing	SD-120108-064-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120108 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1201088090