

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1201098001

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Ultra-Lock (M12) Ethernet Receptacle, 4 Poles, FPM M16, Female (Straight), Panel Mount, D-Code, 0.0195m (.768") Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E200650
General	
Product Family	Industrial Receptacles
Series	120109
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Industrial Ethernet Solutions
Product Name	Ultra-Lock (M12)
Type	Single Ended (pigtail)
UPC	883906516604
Physical	
Coupling Type	Internal Thread
Gender	Female
Keyway	D-coded
Length	0.0195m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M16 x 1.5
Orientation	Straight
Panel Mount	Front
Poles	4
Temperature Range - Operating	-10° to +80°C
Wire Size AWG	22
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	125V
Material Info	
Engineering Number	ERWAAU3000C200
Reference - Drawing Numbers	
Sales Drawing	SD-120109-008-001



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120109 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120109-8001