

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201190026](#)
Status: **Active**
Overview: [Brad Ultra-Lock Connection System](#)
Description: Ultra-Lock (M12) Molded Junction Box with Molded Cable, 8 Port, PNP, 10.0m Cable Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Passive Distribution Boxes
Series [120119](#)
IP Rating IP68
NEMA Rating NEMA 6
Overview [Brad Ultra-Lock Connection System](#)
Product Name Ultra-Lock (M12) Dist Boxes
UPC 78678899580

Physical
Bus I/O Ultra-Lock (M12)
Cable Connector Orientation Straight
Cable Length 10.0m
Home Run Cable Length N/A
Home Run Connector N/A
Home Run Interface N/A
Keyway Single
LED Indicator PNP Sensors
Material - Cable Jacket PUR
Material - Housing PBT
Material - Metal Copper Alloy
Material - Plating Mating Gold over Nickel
Orientation Side Mount
Poles 5
Poles (wired) 4
Ports 8
Temperature Range - Operating -25°C to +90°C
Wiring Configuration Single I/O per Port

Electrical
Current - Maximum per Contact 12.0A per module, 4.0A per port
Functional Wiring PNP
Voltage - Maximum 10-30V DC

Material Info
Engineering Number BKY800P-FBP-10

Reference - Drawing Numbers
Sales Drawing SD-120119-009



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[120119](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1201190026](#)