

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202300153

Status:

Active

Overview:

Brad M23 Signal and Power Connectors

Description:

Brad M23 Signal Connector, Straight Male, Solder Contacts, 17 Poles, Cable Diameter 11.00-17.00mm



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	120230
Application	Signal
Comments	Solder Contacts 0.14-1.00mm2
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906299606
Physical	
Cable Diameter	11.00-17.00mm (.433-.669")
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight
Poles	17
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	8.0A
Voltage - Maximum	150V
Material Info	
Engineering Number	KASJS06-559
Reference - Drawing Numbers	
Sales Drawing	SD-120230-003-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120230 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1202300153](#)