

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202310028

Status:

Active

Overview:

Description:

Brad M23 Signal Connector, Front Panel-Mount Receptacle, Straight Male Flange Mount 4xØ 3.20mm, Solder Contacts, 9 (8+1) Poles

General	
Product Family	Field Attachable / Accessories
Series	120231
Application	Signal
Comments	Solder Contacts 0.14-1.00mm² / 0.75-2.50mm²
IP Rating	IP67
Material - Contact	Brass
Overview	m23_connectivity
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906300036
Physical	
Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	16.329/g
Orientation	Straight
Poles	9 (8+1)
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	20.0A, 8.0A
Voltage - Maximum	300V
Material Info	
Engineering Number	KRS9G26-5531
Reference - Drawing Numbers	
Sales Drawing	SD-120231-002-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120231 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1202310028