

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202530022](#)
Status: **Active**
Overview: [Contrinex Inductive and Photoelectric](#)
Description: Contrinex Inductive Sensor, M8 Housing, 3mm Operating Distance, Embeddable, PNP, NO, 4-pin M12 Connector, 66mm Housing Length

Documents:
[Product Specification 1202530022-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General	
Product Family	Sensors
Series	120253
IP Rating	IP67
Overview	Contrinex Inductive and Photoelectric
Product Category	Inductive Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130061921
Physical	
Connection	Connector (M12, 4-pin)
Length	66mm
Material - Housing	Chrome Plated Nickel Silver
Material - Sensing Face	PBTP (PPS)
Mounting Style	Embeddable
Net Weight	444.000/g
Operating Distance	3mm
Output	NO
Sensor Housing Size	M8
Temperature Range - Operating	-25° to +70°C
Electrical	
Polarity	PNP
Switching Frequency	≤ 1000 Hz
Material Info	
Engineering Number	DW-AS-503-M8
Reference - Drawing Numbers	
Product Specification	1202530022-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed For more information, please visit Contact US	China RoHS 50 Image Not Relevant Not Contained

Search Parts in this Series
[120253](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120253-0022](#)