

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202530058

Status:

Active

Overview:

Contrinex Inductive and Photoelectric

Description:

Contrinex Inductive Sensor, M18 Housing, 12mm Operating Distance, Quasi-embeddable, PNP, NO, 4-pin M12 Connector, 63.5mm Housing Length



Series image - Reference only

Documents:

Product Specification 1202530058-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Sensors
Series	120253
IP Rating	IP67
Overview	Contrinex Inductive and Photoelectric
Product Category	Inductive Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130062287

Physical	
Connection	Connector (M12, 4-pin)
Length	63.5mm
Material - Housing	Chrome Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Quasi-embeddable
Net Weight	648.000/g
Operating Distance	12mm
Output	NO
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +70°C

Electrical	
Polarity	PNP
Switching Frequency	≤ 600 Hz

Material Info	
Engineering Number	DW-AS-503-M18-002

Reference - Drawing Numbers	
Product Specification	1202530058-000

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120253 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120253-0058