

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202540139](#)
Status: **Active**
Overview: [Contrinex Inductive and Photoelectric](#)
Description: [Contrinex Photoelectric Sensor, M18 Housing, Diffuse, PNP, Changeover, Potentiometer Sensitivity Adjustment, 4-pin M12 Connector, 63.5mm Housing Length](#)

Documents:

[Product Specification 1202540139-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	Sensors
Series	120254
IP Rating	IP67
Operating Principle	Diffuse
Overview	Contrinex Inductive and Photoelectric
Product Category	Photoelectric Sensors
Product Name	Contrinex
Type	Photoelectric
UPC	191130068951

Physical

Connection	Connector (M12, 4-pin)
Length	63.5mm
Material - Housing	Chrome Plated Brass
Material - Window	Glass
Output	Changeover
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +55°C

Electrical

Polarity	PNP
Switching Frequency	≤ 1000 Hz

Material Info

Engineering Number	LTS-1180-103
--------------------	--------------

Reference - Drawing Numbers

Product Specification	1202540139-000
-----------------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120254](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120254-0139](#)