

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1203410605

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 26 AWG, Teal Shielded PUR Cable, 5.0m (16.40') Length



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China RoHS

Not Reviewed

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Documents:

Drawing (PDF)

Packaging Specification PK-120341-600-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	120341
Connector End A	RJ-45 (standard)
Connector End B	RJ-45 (standard)
IP Rating	IP20
Material - Contact	Brass
Overview	Brad Industrial Ethernet Solutions
Performance Category	6A
Product Name	Industrial Ethernet
Region	America, Asia, Europe
Type	Double Ended
UPC	887191679068
Physical	
Cable Diameter	6.40mm (.252")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Teal
Coupling Style	Threaded
Gender	Male-Male
Keyway	N/A
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	242.800/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-40° to +70°C
Wire Size AWG	26
Wire/Cable Type	Shielded PUR
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	30V AC / 60V DC
Material Info	
Engineering Number	E66E06020M050
Reference - Drawing Numbers	
Packaging Specification	PK-120341-600-001

Search Parts in this Series

120341 Series

Mates With

120341 Micro-Change CAT6A Receptacles

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1203410605