

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1203410606

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 26 AWG, Teal Shielded PUR Cable, 10.0m (32.81') Length



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Packaging Specification PK-120341-600-001 \(PDF\)](#)

General	
Product Family	Industrial Cordsets
Series	120341
Connector End A	RJ-45 (standard)
Connector End B	RJ-45 (standard)
IP Rating	IP20
Material - Contact	Brass
Overview	Brad Industrial Ethernet Solutions
Performance Category	6A
Product Name	Industrial Ethernet
Region	America, Asia, Europe
Type	Double Ended
UPC	887191679075
Physical	
Cable Diameter	6.40mm (.252")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Teal
Coupling Style	Threaded
Gender	Male-Male
Keyway	N/A
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	1254.000/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-40° to +70°C
Wire Size AWG	26
Wire/Cable Type	Shielded PUR
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	30V AC / 60V DC
Material Info	
Engineering Number	E66E06020M100
Reference - Drawing Numbers	
Packaging Specification	PK-120341-600-001

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

120341 Series

Mates With

120341 Micro-Change CAT6A Receptacles

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1203410606