

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1203410701

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Micro-Change M12 CAT6A Double-Ended Cordset, 8 Poles, Female (Straight) to Male (Straight), 26 AWG, Shielded PUR Cable, 1.0m (3.28') Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Packaging Specification PK-120341-210-001 (PDF)

Agency Certification	
UL	E361772
General	
Product Family	Industrial Cordsets
Series	120341
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Brass
Overview	Brad Industrial Ethernet Solutions
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A
Protocol	N/A
Region	America, Asia, Europe
Type	Double Ended
UPC	887191905211
Physical	
Cable Diameter	6.40mm (.252")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Blue
Coupling Style	Threaded
Gender	Female-Male
Keyway	X-coded
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-40°C to +70°C
Wire Size AWG	26
Wire/Cable Type	Shielded PUR
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	48V
Material Info	
Engineering Number	ERWKEU7020M010
Reference - Drawing Numbers	
Packaging Specification	PK-120341-210-001
Sales Drawing	1203410700-000

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120341 Series

Mates With

120341 Micro-Change CAT6A Plugs and Receptacles

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120341-0701