

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1210010221

Status: **Active**

Overview: mPm DIN Valve Connectors

Description: mPm DIN Adapter, Form A-18mm, Internal Threads, 2 Poles with C4 Circuit, 230V, Yellow LED, A06 Series Light Adapter

Documents:

Drawing (PDF)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	<u>121001</u>
Form	A - 18mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	<u>mPm DIN Valve Connectors</u>
Product Name	mPm
Type	Field Attachable Connector
UPC	883906500641

Physical

Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	23.410/g
Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	230V

Material Info

Engineering Number A06C4M

Reference - Drawing Numbers

Sales Drawing A06XXX, SD-121001-006-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

121001 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1210010221](#)