


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210370058](#)
Status: **Active**
Overview: [mPm DIN Valve Connectors](#)
Description: mPm DIN Valve Connector, Form B-11mm, External Threads, 2 Poles Plus Ground with C4 Circuit, Yellow LED, Black, Nitrile Gasket

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Field Attachable / Accessories
Series	121037
Form	B - 11mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	883906502089
Physical	
Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	41.762/g
Orientation	90° Angle
Pitch - Mating Interface	11.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	5.0A
Voltage - Maximum	24V
Material Info	
Engineering Number	F850B0
Reference - Drawing Numbers	
Sales Drawing	SD-121037-012



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Not Contained Per -ED/01/2017 (12 January 2017) Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[121037](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1210370058](#)