

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1210500554

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form A - 18mm, 2 Pole Plus Ground Position H6/H12 with C4 Circuit, to 1.0m (3.28') PVC Cable Pigtail, Yellow LED, Black Nitrile Gasket, 24V

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E218123
General	
Product Family	Industrial Cordsets
Series	121050
Connector End A	Brad mPm DIN A - 18mm
Connector End B	Pigtail
IP Rating	IP65
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Protocol	N/A
Region	America, Europe
Type	Single Ended
UPC	883906589769
Physical	
Cable Diameter	5.72mm (.225")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	Yellow
Material - Cable Jacket	PVC
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	90.014/g
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	5.0A
Voltage - Maximum	24V
Material Info	
Engineering Number	E452N3N10011C4H
Reference - Drawing Numbers	
Sales Drawing	1210502000-000, SD-121050-001-001



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

121050 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1210500554](#)