

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1210640896

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form A-18mm, PG9 Internal Threads, 2 Pole Plus Ground with R0 Circuit, 24V, VDR Indicator, Black, Nitrile Gasket

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E218123
General	
Product Family	Field Attachable / Accessories
Series	121064
Form	A - 18mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	883906304577
Physical	
Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	14.194/g
Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	24V
Material Info	
Engineering Number	S53209NR021
Reference - Drawing Numbers	
Sales Drawing	1210640896-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per - ED/21/2016 (20 June 2016)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

121064 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1210640896](#)