




13	12	11	10	9	8	7	6	5	4	3	2	1
MATERIAL NO.	ENGINEERING NO.	FINISHED LENGTH										
1300060219	103000A01F0302	3.00 FT +1.75/-0 IN (.9M +44.5/-0mm)										
1300060223	103000A01F0602	6.00 FT +3.50/-0 IN (1.8M +88.9/-0mm)										
1300060234	103000A01F1202	12.00 FT +6.50/-0 IN (3.7M +165.1/-0mm)										
1300060239	103000A01F1502	15.00 FT +6.50/-0 IN (4.6M +165.1/-0mm)										
1300060243	103000A01F2002	20.00 FT +6.50/-0 IN (6.1M +165.1/-0mm)										
1300060248	103000A01F2502	25.00 FT +12.50/-0 IN (7.6M +317.5/-0mm)										



FEMALE FACE VIEW

- NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. ELECTRICAL SPECIFICATIONS
VOLTAGE RATING: 600V AC/DC
CURRENT RATING: 13 AMPS
4. PROTECTION: IP67
5. ASSEMBLY IS RoHS COMPLIANT
BY EXEMPTION

1	GREEN/YELLOW
2	BLACK
3	WHITE

WIRING DIAGRAM

6	1	WRAP LABEL	VINYL	BLACK/YELLOW
5	1	OVERMOLD	PVC	YELLOW
4	1	COUPLING NUT	NYLON	GRAY
3	3	CONTACT SOCKET	Cu ALLOY	GOLD PLATED
2	1	INSERT	PVC	YELLOW
1	A/R	CABLE, 16/3, STOOW	PVC JACKET	YELLOW
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

NEW SALES DOC EC NO: IFG2013-0795 DRAWN: STONE CHK'D: K. JOZWIK APPR: J. MURPHY	2012/11/28	2013/01/16	2013/03/01	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± ---</td><td>± .01</td></tr><tr><td>1 PLACE</td><td>± 0.3</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>± ---</td><td>± ---</td></tr></table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± ---	± .01	1 PLACE	± 0.3	± ---	0 PLACE	± ---	± ---	DIMENSION STYLE IN/MM DRAWN BY DATE RSTONE 2012/11/28 CHECKED BY DATE K. JOZWIK 2013/01/16 APPROVED BY DATE JFMURPHY 2013/03/01 MATERIAL NO. SEE CHART	SCALE 1.5:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
		mm	INCH																								
	4 PLACES	± ---	± ---																								
	3 PLACES	± ---	± ---																								
	2 PLACES	± ---	± .01																								
1 PLACE	± 0.3	± ---																									
0 PLACE	± ---	± ---																									
TITLE MC FEMALE CABLE ASSEMBLY 3 POLE, 16 AWG, STOOV NON-METALIC COUPLING																											
molex																											
DOCUMENT NO. SD-130006-047																											
SHEET NO. 1 OF 1																											
A NEW	DESCRIPTION DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300060233