

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300060298

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change A-Size Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 18 AWG, PVC Cable, 0.91m (3.0') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Cordsets
Series	130006
Connector End A	Mini-Change
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Protocol	N/A
Region	America
Type	Single Ended
UPC	78678843026
Physical	
Cable Diameter	7.14mm (.281")
Cable Length	0.91m (3.0')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	874.000/g
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	18
Wire/Cable Type	UL 2661
Electrical	
Current - Maximum per Contact	10.0A
Voltage - Maximum	300V
Material Info	
Engineering Number	103000A03F030
Reference - Drawing Numbers	
Sales Drawing	SD-130006-029, SD-130006-070-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
130006 Series

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300060298