

103006K20M010E

OVERMOLD COLOR = RED

LENGTH
M001 = .1 METER
M010 = 1 METER
M100 = 10 METER

- NOTES:
- MATERIAL: AS NOTED
 - FINISH: AS NOTED
 - ELECTRICAL:
CURRENT RATING: 15A
VOLTAGE : 500V PER IEC 60664
VOLTAGE: 600V PER UL 2237
 - TEMP RATING: -20°TO +90°C
 - PROTECTION: IP67 (WHEN MATED)
 - UL 2237 & CULUS LISTED, FILE NO. E258922
 - ALL DIMS ARE FOR REFERENCE
UNLESS NOTED OTHERWISE



7	WARNING LABEL	VINYL	ORANGE
6	WRAP LABEL	VINYL	BLACK/YELLOW
5	OVERMOLD	PVC	RED
4	COUPLING	ZINC DIE-CAST	BLACK
3	CONTACT PIN	COPPER ALLOY	GOLD PLATED
2	MALE INSERT (A-SIZE)	PVC	BLACK
1	CABLE, 14/3 TC-ER	TPE JACKET	BLACK
ITEM	DESCRIPTION	MATERIAL	FINISH

IEC VOLTS WAS 400, ADD CHART AND TOLS	EC NO: IPG2017-0882	DRWN: RSTONE 3/29/17	CH'KD: MZIELIN 2017/04/10	APPR: BWOODMAN2014/12/08
REV	B1	DESCRIPTION	DESCRIPTION	DESCRIPTION

QUALITY SYMBOL
▽=0
▽C=0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±---
1 PLACE	±---	±---
ANGULAR ±---°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
INCH	
DRAWN BY	DATE
BARDEN	2014/11/26
CHECKED BY	DATE
RSTONE	2014/12/5
APPROVED BY	DATE
JFMURPHY	2014/12/08
MATERIAL NO. ---	
SIZE	C

SCALE NTS	DESIGN UNITS INCH		THIRD ANGLE PROJECTION
TITLE MINI-CHANGE ASSEMBLY 3P M/MP STRAIGHT #14AWG CABLE			
		MOLEX INCORPORATED	
DOCUMENT NO. SD-130061-028			SHEET NO. 1 OF 1
CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300062404