

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300070036](#)
Status: **Active**
Overview:
Description: Mini-Change B-Size Single-Ended Cordset, 6 Poles, Female (Straight) to Pigtail, 16 AWG, PVC Cable, 15.24m (50.0') Length

Agency Certification

CSA	LR6837
UL	E152210

General

Product Family	Industrial Cordsets
Series	130007
Connector End A	Mini-Change
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	minichange_products
Product Name	Mini-Change
Protocol	DeviceNet
Region	America
Type	Single Ended
UPC	78678850913

Physical

Cable Diameter	13.72mm (.540")
Cable Length	15.24m (50.0')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	6
Temperature Range - Operating	-20° to +105°C
Wire Size AWG	16
Wire/Cable Type	STOOW

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V

Material Info

Engineering Number	206000A01F500
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-130007-001-001
---------------	-------------------

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130007](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300070036](#)