

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300080157

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change C-Size Single-Ended Cordset, 12 Poles, Female (Straight) to Pigtail, 16 AWG, PVC Cable, 1.83m (6.0') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR6837
UL		E152210
General		
Product Family		Industrial Cordsets
Series		130008
Connector End A		Mini-Change
Connector End B		Pigtail
IP Rating		IP67
Material - Contact		Brass
Overview		Brad Mini-Change Connectors
Product Name		Mini-Change
Protocol		DeviceNet
Region		America
Type		Single Ended
UPC		78678807737
Physical		
Cable Diameter		18.03mm (.710")
Cable Length		1.83m (6.0')
Color - Cable Jacket		Yellow
Coupling Style		Threaded
Gender		Female-Pigtail
Keyway		Single
LED Indicator		No
Material - Cable Jacket		PVC
Material - Connector Body		TPE
Material - Coupling Nut		Black Epoxy Coated Zinc
Material - Plating Mating		Gold
Net Weight		342.000/g
Orientation		Straight to Pigtail
Poles		12
Temperature Range - Operating		-20°C to +105°C
Wire Size AWG		16
Wire/Cable Type		STOOW
Electrical		
Current - Maximum per Contact		5.0A
Voltage - Maximum		600V
Material Info		
Engineering Number		302000A01F060
Reference - Drawing Numbers		
Sales Drawing		SD-130008-014-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

130008 Series

This document was generated on 08/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300080157](#)