

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300080338

Status:

Active

Overview:

Description:

Mini-Change C-Size Single-Ended Cordset, 9 Poles, Female (Straight) to Pigtail, 16 AWG, PVC Cable, 10.67m (35.0') Length

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Cordsets
Series	130008
Connector End A	Mini-Change
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	minichange_products
Product Name	Mini-Change
Protocol	DeviceNet
Region	America
Type	Single Ended
UPC	78678843489
Physical	
Cable Diameter	16.26mm (.640")
Cable Length	10.67m (35.0')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	9
Temperature Range - Operating	-20° to +105°C
Wire Size AWG	16
Wire/Cable Type	STOOW
Electrical	
Current - Maximum per Contact	7.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	309000A01F350
Reference - Drawing Numbers	
Sales Drawing	SD-130008-004-001

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300080338