

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300100106

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 10.0m (32.81') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E152210

General

Product Family

Industrial Cordsets

Series

130010

Connector End A

Mini-Change

Connector End B

Mini-Change

IP Rating

IP67

Material - Contact

Copper Alloy

Overview

Brad Mini-Change Connectors

Product Name

Mini-Change

Protocol

DeviceNet

Region

America

Type

Double Ended

UPC

78678808175

Physical

Cable Diameter

12.70mm (.500")

Cable Length

10.0m (32.81')

Color - Cable Jacket

Yellow

Coupling Style

Threaded

Gender

Female-Male

Keyway

Single

LED Indicator

No

Material - Cable Jacket

TPE

Material - Connector Body

TPE

Material - Coupling Nut

Black Epoxy Coated Zinc

Material - Plating Mating

Gold

Net Weight

1767.922/g

Orientation

Straight to Straight

Poles

5

Temperature Range - Operating

-20° to +105°C

Wire Size AWG

16

Wire/Cable Type

TC-ER

Electrical

Current - Maximum per Contact

8.0A

Voltage - Maximum

600V

Material Info

Engineering Number

115030K13M100

Reference - Drawing Numbers

Sales Drawing

SD-130010-017-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

130010 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300100106