

F

E

D

C

B

A

F


E

D

C

B

A



CENELEC EN 50 044 PINOUT SHOWN
(SAE-J-1738A SHOWN IN PARENTHESIS)

4 (1)	BLACK	4 (1)
3 (2)	WHITE	3 (2)
1 (3)	RED	1 (3)
2 (4)	GREEN/YELLOW	2 (4)

SPECIFICATION DATA

COMPONENT	MATERIAL	FINISH
LABEL	VINYL	BLACK/YELLOW
COUPLER	ZINC	BLACK ELECTROPHORETIC COATING
CONTACT	COPPER ALLOY	Au OVER Ni
INSERT	PVC	YELLOW
OVERMOLD	PVC	YELLOW
CABLE #16/4	PVC	YELLOW
VOLTAGE RATING:		600V
AMPERAGE RATING:		10A
PROTECTION CLASS:		IP 67

114033A01MXXX

cable type
#16/4 C AWG
STOOW/ST YELLOW

finish length
M005---.5 Meters
M010---1 Meters
M200---20 Meters

RELEASED EC NO: IPG2016-0384 DRWN: GGUSTAFS 2015/09/08 CHKD: BARDEN 2015/11/19 APPR: BWOODMAN2015/10/30	DESCRIPTION	QUALITY SYMBOLS <div>▽=0</div> <div>▽C=0</div>	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION					
				mm	INCH	IN/MM		NTS	INCH						
			4 PLACES	±---	±---	DRAWN BY	DATE	TITLE MINI-CHANGE CORDSET 4P MALE/FEMALE 90/90 #16/4 AWG PVC CABLE							
			3 PLACES	±---	±---	GGUSTAFS	2015/09/08								
			2 PLACES	±---	±---	CHECKED BY	DATE								
			1 PLACE	±---	±---	BARDEN	2015/11/19								
			ANGULAR ±.5°			APPROVED BY		DATE	molex MOLEX INCORPORATED						
						BWOODMAN		2015/10/30							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.						SHEET NO.	
						SEE MATRIX		SD-130010-034						1 OF 1	
SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
A	REV														

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300100961