


- NOTES:
- 1. ELECTRICAL:
 - VOLTAGE RATING PER IEC 60664: 300V
 - VOLTAGE RATING PER UL: 300V
 - CURRENT: 8A
 - 2. TEMP RATING: -25° TO +80°C
 - 3. PROTECTION: IP67 (WHEN MATED)
 - 4. COUPLING THREAD" 7/8-16
 - 5. AGENCY:
 - UL RECOGNIZED, FILE: E152210
 - CSA CERTIFICATION FILE: LR6837
 - 6 ALL DIMS ARE FOR REFERENCE UNLES NOTED OTHERWISE
 - 7. PART NUMBER WITH "H" HAVE TWO ID MARKERS ONE ON EACH END

WIRING DIAGRAM






PART No. MATRIX

DN11A-XXXXX

Units:
M = Meter

Length
Examples:
005 = 0.5 m
010 = 1 m
050 = 5 m
100 = 10 m
150 = 15 m

OPTIONAL:
H= ID CARRIER



BILL OF MATERIALS

13	2	ID CARRIER	PVC	-
12	1	LABEL WRAP	VINYL	YELLOW
11	1	COUPLING NUT A-SIZE EXT.	ZINC	BLACK
10	2	PIN CONTACT 16 AWG	COPPER	GOLD OVER Ni-PLATED
9	3	PIN CONTACT 18 AWG	COPPER	GOLD OVER Ni-PLATED
8	1	HOUSING A-SIZE 5P MALE	ARNITEL	BLACK
7	1	FRICTION RING A-SIZE	NYLON	GRAY
6	1	MC COUPLING NUT A-SIZE	ZINC	BLACK
5	2	MC SOCKET SLEEVE ASSY 16 AWG	COPPER	GOLD OVER Ni-PLATED
4	3	MC SOCKET SLEEVE ASSY 18 AWG	COPPER	GOLD OVER Ni-PLATED
3	1	HOUSING A-SIZE 5P FEMALE	ARNITEL	BLACK
2	-	MOULDING MATERIAL	ARNITEL	BLACK
1	-	TRUNK CABLE 19X30 AWG OD=12	PVC	GRAY
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH/COLOR

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
FA= 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: INSERT AND OVM MATERIAL CHANGE					molex							
	mm		1:1														
FE= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 651030 DRWN: MKOWALCZYK01 2020/04/27 CHK'D: ASZELAG 2020/12/09 APPR: DSTACHOWIAK 2020/12/10 INITIAL REVISION: DRWN: MKOWALCZYK01 2018/09/07 APPR: MMATLA 2018/09/11												
FE= 0	ANGULAR TOL ± °																
FD= 0	4 PLACES		±														
	3 PLACES		±														
	2 PLACES		± 0.05														
	1 PLACE		± 0.3														
DIVISIONAL SYMBOLS	0 PLACES		± 0.5														
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION
						A3-SIZE		130025		1300250051		PSD		000		B	
										MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
										SEE SHEET 2		GENERAL MARKET		1 OF 2			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300250076](#) [1300250071](#) [1300250079](#) [1300250085](#) [1300250103](#) [1300250108](#) [1300250058](#) [1300250081](#)
[1300250090](#) [1300250091](#) [1300250122](#)