

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300390549

Status:

Active

Overview:

DeviceNet Solutions

Description:

DeviceNet D-Net Open with Screws to Micro-Change (M12) Cordset, 5 Poles, Female (Straight) to Male (90°), DeviceNet Thin High Flex Stranded Cable, 22 AWG, PVC Cable, 1.0m (3.28') Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
General	
Product Family	Industrial Cordsets
Series	130039
Connector End A	D-Net Open
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	DeviceNet Solutions
Product Name	DeviceNet Trunk, Mini-Change
Region	Europe
Type	Double Ended
UPC	78172514731
Physical	
Cable Diameter	N/A
Cable Length	1.0m (3.28')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	Polyamide
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire Size AWG	22
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	300V AC/DC
Material Info	
Engineering Number	DNDF43A-M010
Reference - Drawing Numbers	
Sales Drawing	SD-130039-059-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130039 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300390549