

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300480048](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Micro-Change (M12) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 22 AWG, PUR Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Cordsets
Series [130048](#)
Connector End A Micro-Change (M12)
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Industrial Ethernet Solutions](#)
Performance Category 5e
Product Name Micro-Change (M12)
Protocol N/A
Region America, Asia, Europe
Type Single Ended
UPC 78678804010

Physical

Cable Diameter 5.59mm (.220")
Cable Length 5.0m (16.40')
Color - Cable Jacket Teal
Coupling Style Threaded
Gender Male-Pigtail
Keyway D-coded
LED Indicator No
Material - Cable Jacket PUR
Material - Connector Body PUR
Material - Coupling Nut Nickel-plated Brass
Material - Plating Mating Gold
Orientation Straight to Pigtail
Poles 4
Temperature Range - Operating -20°C to +75°C
Wire Size AWG 22
Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 1.5A
Voltage - Maximum 30V

Material Info

Engineering Number E10A00610M050

Reference - Drawing Numbers

Sales Drawing SD-120108-014



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[130048](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300480048