

#### NOTES:

- 1) MATERIAL: SEE TABLE
- 2) FINISHES: SEE TABLE
- 3) WRAP LABEL IS MARKED WITH P/N, DATE CODE  
VOLTAGE & AMPERAGE
- 4) MATES WITH: MINI CHANGE ALT-KEY, 4 POLE RECEPTACLE
- 5) ELECTRICAL DATA:  
14AWG UL TYPE: TC-ER STRANDED CABLE  
POLES: 4  
MAX VOLTAGE: 600V  
MAX CURRENT: 15A  
PROTECTION IP67  
TEMPERATURE RANGE: -20°C TO 90°C
- 6) PACKAGING:  
CABLE ASSEMBLIES ARE BAGGED SEPERATLY IN POLY BAGS  
WITH BAR CODE LABEL ATTACHED TO OUTSIDE OF BAG.
- 7) ASSEMBLY IS RoHS COMPLIANT
- 8) AGENCY CERTIFICATIONS:  
UL 2237 LISTED, E258922

S1		P1
1	BLACK #1	1
2	BLACK #2	2
3	BLACK #3	3
4	GREEN/YELLOW OR GREEN	4

WIRING DIAGRAM

114130K21M020

cable type  
TC-ER  
14/4C AWG  
BLACK

cable length  
010----1 Meters  
020----2 Meters  
100----10 Meters  
ETC.---

DESCRIPTION	MATERIAL	FINISH
WARNING LABEL	MYLAR	N/A
LABEL	MYLAR	BLACK/YELLOW
FEMALE INSERT	PVC	BLACK
FEMALE COUPLING NUT	ZINC ALLOY	BLACK E-COATED
SOCKET CONTACT	CU ALLOY	GOLD PLATE
OVERMOLD	PVC	BLACK
MALE INSERT	PVC	BLACK
MALE COUPLING NUT	ZINC ALLOY	BLACK E-COATED
PIN CONTACT	Cu ALLOY	GOLD PLATE
CABLE 14AWG-TC-ER	TPE	BLACK




REVISED TEXT EC NO: IPG2015-1959 DRWNGGUSTAFSON 2015/05/13 CHKD:BARDEN 2015/06/30 APPR:BWODMAN 2015/09/18	DESCRIPTION REV
---	--------------------

QUALITY SYMBOLS ▽=0 ▽=0
----------------------------------

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ± ---	± ---
3 PLACES ± ---	± .005
2 PLACES ± 0.13	± .010
1 PLACE ± 0.25	± .020
ANGULAR ± 1/2°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE IN/MM	
DRAWN BY BRUPERT	DATE 2011/07/11
CHECKED BY TWOLEDGE	DATE 2014/08/07
APPROVED BY BWODMAN	DATE 2014/09/04
MATERIAL NO.	
SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE 15:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
TITLE MC 4P FEM/MALE STR/STR 4 POLE ALT KEY 14-4 TC ER BLACK CABLE		
MOLEX MOLEX INCORPORATED		
DOCUMENT NO. SD-130062-022		SHEET NO. 1 OF 1



#### NOTES:

- 1) MATERIAL: SEE TABLE
- 2) FINISHES: SEE TABLE
- 3) WRAP LABEL IS MARKED WITH P/N, DATE CODE  
VOLTAGE & AMPERAGE
- 4) MATES WITH: MINI CHANGE ALT-KEY, 4 POLE RECEPTACLE
- 5) ELECTRICAL DATA:  
14AWG UL TYPE: TC-ER STRANDED CABLE  
POLES: 4  
MAX VOLTAGE: 600V  
MAX CURRENT: 15A  
PROTECTION IP67  
TEMPERATURE RANGE: -20°C TO 90°C
- 6) PACKAGING:  
CABLE ASSEMBLIES ARE BAGGED SEPERATLY IN POLY BAGS  
WITH BAR CODE LABEL ATTACHED TO OUTSIDE OF BAG.
- 7) ASSEMBLY IS RoHS COMPLIANT
- 8) AGENCY CERTIFICATIONS:  
UL 2237 LISTED, E258922

S1		P1
1	BLACK #1	1
2	BLACK #2	2
3	BLACK #3	3
4	GREEN/YELLOW OR GREEN	4

WIRING DIAGRAM

114130K21M020

cable type  
TC-ER  
14/4C AWG  
BLACK

cable length  
010----1 Meters  
020----2 Meters  
100----10 Meters  
ETC.---

WARNING LABEL	MYLAR	N/A
LABEL	MYLAR	BLACK/YELLOW
FEMALE INSERT	PVC	BLACK
FEMALE COUPLING NUT	ZINC ALLOY	BLACK E-COATED
SOCKET CONTACT	CU ALLOY	GOLD PLATE
OVERMOLD	PVC	BLACK
MALE INSERT	PVC	BLACK
MALE COUPLING NUT	ZINC ALLOY	BLACK E-COATED
PIN CONTACT	Cu ALLOY	GOLD PLATE
CABLE 14AWG-TC-ER	TPE	BLACK
DESCRIPTION	MATERIAL	FINISH

REVISED TEXT EC NO: IPG2015-1959 DRWNGGUSTAFSON 2015/05/13 CHKD:BARDEN 2015/06/30 APPR:BWODMAN 2015/09/18
---

QUALITY SYMBOLS ▽=0 ▽=0
----------------------------------

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± .005
2 PLACES ± 0.13 ± .010
1 PLACE ± 0.25 ± .020
ANGULAR ± 1/2°
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE IN/MM
DRAWN BY DATE BRUPERT 2011/07/11
CHECKED BY DATE TWOLEDGE 2014/08/07
APPROVED BY DATE BWODMAN 2014/09/04
MATERIAL NO.
SIZE C

SCALE 15:1
DESIGN UNITS INCH
THIRD ANGLE PROJECTION
TITLE MC 4P FEM/MALE STR/STR 4 POLE ALT KEY 14-4 TC ER BLACK CABLE
MOLEX MOLEX INCORPORATED
DOCUMENT NO. SD-130062-022
SHEET NO. 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300620281