

F

E


D

C

B


A

FRONT VIEW - FEMALE INSERT




- 1 BLACK #1
- 2 BLACK #2
- 3 BLACK #3
- 4 GREEN/YELLOW

FRONT VIEW - MALE INSERT



- 1 BLACK #1
- 2 BLACK #2
- 3 BLACK #3
- 4 GREEN/YELLOW



MECHANICAL

CONTACT : GOLD/NICKEL OVER COPPER ALLOY  
INSERT : BLACK PVC  
COUPLING NUT: ZINC DIE CAST, BLACK E-COAT  
MOLDED BODY: BLACK PVC  
CABLE: 14 AWG 4 CONDUCTORS BLACK TPE JACKET  
CABLE MARKING: [MFG. UL FILE NO.] 14 AWG (2.08mm<sup>2</sup>)  
UL TYPE TC-ER/MTW (UL) THHN/THWN  
600V 90C DRY 75C WET OIL RES SUN  
RES [MFG. CSA FILE NO.] CSA AWM  
I/II A/B 105C W75 1000V -40C FT4

ELECTRICAL

VOLTAGE RATING: 600V AC/DC  
AMPERAGE: 15A



ENVIRONMENTAL

PROTECTION: IP67

114030K21MXXXG

Cable type  
14/4 AWG  
black TPE

Finished Length  
M005 = .5 Meters  
M010 = 1 Meter

UPDATED DRAWING EC NO: IPG2016-1628 DRWN: GGUSTAFS 2016/06/02 CHKD: MZIELINS 2016/06/15 APPR: BWOODMAN2015/11/09  B	DESCRIPTION          REV	QUALITY SYMBOLS  ▽=0  ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE INCH/MM		SCALE NTS	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY KCOX01	DATE 2015/10/19	TITLE  MINI CHANGE ASSEMBLY 4P MALE/FEMALE 14/4 AWG TPE BLACK				
			4 PLACES	±---	±---	CHECKED BY BARDEN	DATE 2015/10/19					
			3 PLACES	±---	±---	APPROVED BY JFMURPHY	DATE 2015/11/09				 MOLEX INCORPORATED	
			2 PLACES	±---	±---	MATERIAL NO. SEE MATRIX						DOCUMENT NO. SD-130062-023
			1 PLACE	±---	±---	ANGULAR ±---°						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									
						SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300621157