



13	12	11	10	9	8	7	6	5	4	3	2	1
POLES	MATERIAL NO.	ENG. NO.	LENGTH									
3	1300630003	C03000A48M020	2M +89-0MM (6'7"+3.50-0)									
4	1300630089	C04000A48M020	2M +89-0MM (6'7"+3.50-0)									

FACE VIEW-FEMALE INSERT



SPECS:
OVERMOLD: GRAY PVC
INSERT: BLACK PVC
COUPLING NUT: ANODIZED ALUMINUM
CABLE: #10AWG GRAY PVC
DUAL RATED UL TC/OPEN WIRING & STOOV
ELECTRICAL: 600V AC/DC 32 AMPS

UPDATED DRAWING EC NO: IPG2014-1095 DRAWING:GUSTAFSON 2015/09/01 CHKD:VOU 2015/11/12 APPR:JFMURPHY 2015/09/16				QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE IN/MM				SCALE 1:1		DESIGN UNITS INCH		THIRD ANGLE PROJECTION					
B	DESCRIPTION	4 PLACES ± --- ± ---			mm	INCH	DRAWN BY B. RUPERT		DATE 01/12/10		TITLE QUICK CHANGE FEMALE STRAIGHT 3 & 4 POLE AS PORTABLES											
		3 PLACES ± --- ± ---					CHECKED BY		DATE													
		2 PLACES ± --- ± ---					B. WOODMAN		01/12/10													
		1 PLACE ± --- ± ---					APPROVED BY		DATE		MOLEX MOLEX INCORPORATED											
		ANGULAR ±1/2°					JFMURPHY		2010/01/15													
REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				MATERIAL NO.				DOCUMENT NO.				SHEET NO. 1 OF 1								
						SEE CHART				SD-130063-089												
									SIZE C				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300630131](#)