



13	12	11	10	9	8	7	6	5	4	3	2	1
----	----	----	----	---	---	---	---	---	---	---	---	---

POLES	MATERIAL NO.	ENG. NO.	LENGTH
3	1300630003	C03000A48M020	2M +89-0MM (6'7"+3.50-0)
4	1300630089	C04000A48M020	2M +89-0MM (6'7"+3.50-0)

FACE VIEW-FEMALE INSERT



SPECS:
OVERMOLD: GRAY PVC
INSERT: BLACK PVC
COUPLING NUT: ANODIZED ALUMINUM
CABLE: #10AWG GRAY PVC
DUAL RATED UL TC/OPEN WIRING & STOOV
ELECTRICAL: 600V AC/DC 32 AMPS

UPDATED DRAWING EC NO: IPG2014-1095 DRAWING:GUSTAFSON 2015/09/01 CHKD:VOU 2015/11/12 APPR:JFMURPHY 2015/09/16			QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
B	DESCRIPTION			mm	INCH	DRAWN BY B.RUPERT	DATE 01/12/10	TITLE QUICK CHANGE FEMALE STRAIGHT 3 & 4 POLE AS PORTABLES					
		4 PLACES		± ---	± ---	CHECKED BY B.WOODMAN	DATE 01/12/10						
		3 PLACES		± ---	± ---	APPROVED BY JFMURPHY		DATE 2010/01/15	MOLEX INCORPORATED				
		2 PLACES		± ---	± ---								
		1 PLACE		± ---	± ---								
		ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-130063-089		1 OF 1					
	REV					SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300630255