


13	12	11	10	9	8	7	6	5	4	3	2	1
POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH								
3	1300640065	CC3030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640187	CC4030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640245	CC4030A48M100	32	10M +318-0MM (32'10" +12.5*-0")								



SPECs: OVERMOLD: GRAY PVC INSERT: BLACK PVC COUPLING NUT: ANODIZED ALUMINUM CABLE: #10AWG GRAY PVC DUAL RATED UL TC/OPEN WIRING & STOOV ELECTRICAL: 600V AC/DC		ADDED PART NUMBER EC NO: IPG2016-1155 DRWNGGUSTAFSON 2016/02/23 CHKDHZIELINSKI 2016/03/15 APPR:BMWOODMAN 2016/02/23 DESCRIPTION REV		QUALITY SYMBOLS ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED) <table><thead><tr><th></th><th>mm</th><th>INCH</th></tr></thead><tbody><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± .005</td></tr><tr><td>2 PLACES</td><td>± ---</td><td>± .010</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± .020</td></tr></tbody></table> ANGULAR ±1/2°			mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .005	2 PLACES	± ---	± .010	1 PLACE	± ---	± .020	DIMENSION STYLE IN/MM DRAWN BY DATE B.RUPERT 01/12/10 CHECKED BY DATE B.WOODMAN 01/12/10 APPROVED BY DATE JFMURPHY 2010/01/15 MATERIAL NO. DOCUMENT NO.		SCALE 1:2 DESIGN UNITS INCH THIRD ANGLE PROJECTION		QUICK CHANGE FEMALE/MALE STRAIGHT 3 & 4 POLE AS PORTABLES  MOLEX INCORPORATED SHEET NO. 1 OF 1	
	mm	INCH																										
4 PLACES	± ---	± ---																										
3 PLACES	± ---	± .005																										
2 PLACES	± ---	± .010																										
1 PLACE	± ---	± .020																										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE CHART				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300640069