


13	12	11	10	9	8	7	6	5	4	3	2	1
POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH								
3	1300640065	CC3030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640187	CC4030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640245	CC4030A48M100	32	10M +318-0MM (32'10" +12.5*-0")								



SPECS:
OVERMOLD: GRAY PVC
INSERT: BLACK PVC
COUPLING NUT: ANODIZED ALUMINUM
CABLE: #10AWG GRAY PVC
DUAL RATED UL TC/OPEN WIRING & STOOV
ELECTRICAL: 600V AC/DC

ADDED PART NUMBER EC NO: IPG2016-1155 DRWNGGUSTAFSON 2016/02/23 CHKCHZIELINSKI 2016/03/15 APPR:BMWOODMAN 2016/02/23	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:2	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY B.RUPERT	DATE 01/12/10	TITLE QUICK CHANGE FEMALE/MALE STRAIGHT 3 & 4 POLE AS PORTABLES MOLEX INCORPORATED				
			4 PLACES	± ---	± ---	CHECKED BY B.WOODMAN	DATE 01/12/10					
			3 PLACES	± ---	±.005	APPROVED BY JFMURPHY	DATE 2010/01/15					
			2 PLACES	± ---	±.010	MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
			1 PLACE	± ---	±.020	SEE CHART		SD-130064-065		1 OF 1		
			ANGULAR ±1/2°			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						
			SIZE									
			C									
			REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300640275