





13	12	11	10	9	8	7	6	5	4	3	2	1
----	----	----	----	---	---	---	---	---	---	---	---	---

POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH
3	1300640401	CC3130A48M020	32	2M +89-0MM (6'7"+3.50-0)
4	1300640356	CC4130A48M020	32	2M +89-0MM (6'7"+3.50-0)



SPECS:
OVERMOLD: GRAY PVC
INSERT: BLACK PVC
COUPLING NUT: ANODIZED ALUMINUM
CABLE: #10AWG GRAY PVC
DUAL RATED UL TC/OPEN WIRING & STOOO
ELECTRICAL: 600V AC/DC

UPDATED PROFILE EC NO: IPG2014-1160 DRAWNGGUSTAFSON 2013/12/26 CHKD:VOU 2014/01/15 APPR:BWODMAN 2014/05/12		DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY B.RUPERT	DATE 01/12/10	TITLE QUICK CHANGE FEM/MALE STRAIGHT, ALT KEY 3 & 4 POLE AS PORTABLES			
				4 PLACES	± ---	± ---	CHECKED BY B.WOODMAN	DATE 01/12/10				
				3 PLACES	± ---	±.005	APPROVED BY JFMURPHY	DATE 2010/01/15				
				2 PLACES	± ---	±.010	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-130064-401		SHEET NO. 1 OF 1	
				1 PLACE	± ---	±.020	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
				ANGULAR ±1/2°								
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300640384