





13	12	11	10	9	8	7	6	5	4	3	2	1
----	----	----	----	---	---	---	---	---	---	---	---	---

POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH
3	1300640401	CC3130A48M020	32	2M +89-0MM (6'7"+3.50-0)
4	1300640356	CC4130A48M020	32	2M +89-0MM (6'7"+3.50-0)



SPECS:
OVERMOLD: GRAY PVC
INSERT: BLACK PVC
COUPLING NUT: ANODIZED ALUMINUM
CABLE: #10AWG GRAY PVC
DUAL RATED UL TC/OPEN WIRING & STOOO
ELECTRICAL: 600V AC/DC

UPDATED PROFILE EC NO: IPG2014-1160 DRAWNGGUSTAFSON 2013/12/26 CHKD:VOU 2014/01/15 APPR:BWODMAN 2014/05/12	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY B.RUPERT	DATE 01/12/10	TITLE QUICK CHANGE FEM/MALE STRAIGHT, ALT KEY 3 & 4 POLE AS PORTABLES			
			4 PLACES ± --- ± ---	3 PLACES ± --- ± .005	CHECKED BY B.WOODMAN	DATE 01/12/10					
			2 PLACES ± --- ± .010	1 PLACE ± --- ± .020	APPROVED BY JFMURPHY	DATE 2010/01/15	molex MOLEX INCORPORATED				
			ANGULAR ±1/2°		MATERIAL NO.				DOCUMENT NO.		SHEET NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-130064-401		1 OF 1		
			B		C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300640386