



WIRING DIAGRAM

NOTES:

- 1) MATERIAL: SEE TABLE
- 2) FINISHES: SEE TABLE
- 3) WRAP LABEL IS MARKED WITH P/N, DATE CODE VOLTAGE & AMPERAGE
- 4) MATES WITH: QUICK CHANGE 3 POLE RECEPTACLE
- 5) ELECTRICAL DATA:
10AWG UL TYPE: TC-ER STRANDED CABLE
MAX VOLTAGE: 600V
MAX CURRENT: 32A
PROTECTION IP67 (WHEN MATED)
TEMPERATURE RANGE: -20°C TO 90°C
- 6) PACKAGING:
CABLE ASSEMBLIES ARE BAGGED SEPERATLY IN POLY BAGS
WITH BAR CODE LABEL ATTACHED TO OUTSIDE OF BAG.
- 7) ASSEMBLY IS RoHS COMPLIANT



MALE FACE VIEW

PART NUMBER LEGEND

CC3033K19MXXXE

- DOUBLE END
- POLE COUNT: 3
- OC FEMALE 90 DEG/MALE 90 DEG
- CABLE TYPE: 10 AWG TC ER, BLACK
- OVERMOLD COLOR: RED
- FINISHED LENGTH:
M001= .1M
M010= 1.0M
M100= 10.0M

11	2	WARNING LABEL	VINYL	ORANGE/BLACK
10	1	WRAP LABEL	VINYL	BLACK/YELLOW
9	1	OVERMOLD (MALE 90 DEG)	PVC	RED
8	1	COUPLING (MALE)	ALUMINUM	CLEAR ANNODIZE
7	3	CONTACT PIN	Cu ALLOY	GOLD PLATED
6	1	INSERT (MALE)	PVC	BLACK
5	1	OVERMOLD (FEMALE 90 DEG)	PVC	RED
4	1	COUPLING	ALUMINUM	CLEAR ANNODIZE
3	3	CONTACT SOCKET	Cu ALLOY	GOLD PLATED
2	1	INSERT	PVC	BLACK
1	1	CABLE, 10/3 TC-ER (SEE NOTE 5)	TPE JACKET	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	DESCRIPTION

RELEASED EC NO: IPG2016-0830 DRAWN: RSTONE CHKD: CHKD: APPR: BWOODMAN REV: A	DESCRIPTION 2015/12/18 2016/02/29	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY RSTONE	DATE 2015/12/18	TITLE QUICK CHANGE CORD ASSY FEM 90D TO MALE 90D, RED 10AWG TPE CABLE	
			4 PLACES	± ---	± ---	CHECKED BY	DATE		
			3 PLACES	± ---	± ---				
			2 PLACES	± ---	± .01			molex	
			1 PLACE	± 0.3	± ---	APPROVED BY	DATE		
			0 PLACE	± ---	± ---	BWOODMAN	2016/02/29		
			ANGULAR ± .5 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		- SIZE C		SD-130064-011 1 OF 1		
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300640467