


13	12	11	10	9	8	7	6	5	4	3	2	1
POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH								
3	1300640065	CC3030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640187	CC4030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640245	CC4030A48M100	32	10M +318-0MM (32'10" +12.5*-0")								



SPECs: OVERMOLD: GRAY PVC INSERT: BLACK PVC COUPLING NUT: ANODIZED ALUMINUM CABLE: #10AWG GRAY PVC DUAL RATED UL TC/OPEN WIRING & ST00W ELECTRICAL: 600V AC/DC		<div>ADDED PART NUMBER EC NO: IPG2016-1155 DRAWNGGUSTAFSON 2016/02/23 CHKD:HZIELINSKI 2016/03/15 APPR:BMWOODMAN 2016/02/23</div>		<div>QUALITY SYMBOLS ▽=0 ▽=0</div>		<div>GENERAL TOLERANCES (UNLESS SPECIFIED)<table><thead><tr><th></th><th>mm</th><th>INCH</th></tr></thead><tbody><tr><td>4 PLACES</td><td>± .---</td><td>± .---</td></tr><tr><td>3 PLACES</td><td>± .---</td><td>± .005</td></tr><tr><td>2 PLACES</td><td>± .---</td><td>± .010</td></tr><tr><td>1 PLACE</td><td>± .---</td><td>± .020</td></tr></tbody></table>ANGULAR ±1/2°</div>			mm	INCH	4 PLACES	± .---	± .---	3 PLACES	± .---	± .005	2 PLACES	± .---	± .010	1 PLACE	± .---	± .020	<div>DIMENSION STYLE IN/MM</div> <div>DRAWN BY DATE B.RUPERT 01/12/10</div> <div>CHECKED BY DATE B.WOODMAN 01/12/10</div> <div>APPROVED BY DATE JFMURPHY 2010/01/15</div>		<div>SCALE 1:2</div> <div>DESIGN UNITS INCH</div> <div>THIRD ANGLE PROJECTION</div>		<div>QUICK CHANGE FEMALE/MALE STRAIGHT 3 & 4 POLE AS PORTABLES</div>	
	mm	INCH																										
4 PLACES	± .---	± .---																										
3 PLACES	± .---	± .005																										
2 PLACES	± .---	± .010																										
1 PLACE	± .---	± .020																										
						<div>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</div>		<div>MATERIAL NO. SEE CHART</div>		<div>DOCUMENT NO. SD-130064-065</div>		<div>SHEET NO. 1 OF 1</div>																
								<div>THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</div>																				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300642018