

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300830280

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead POW-R-MITE Industrial Duty Cable Reel, 14/3 SOOW, 10.67m (35.0') Cord Length, with 20A Pendant Outlet Box and Ball Stop

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR29921

General

Product Family

Series

Cable Length

Comments

Depth

Duty

Enclosure Rating

Height

NEMA Configuration

Overview

Product Name

Type

UPC

Width

Electric Reels

130083

N/A

Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.

0.34m (13.50")

Industrial

NEMA 4

0.39m (15.32")

NEMA 5-20

Reels - Woodhead

POW-R-MITE

Cable Reel

78678888680

254.00mm (10.00")

Physical

Cable Movement

Cord Length

Drum Lock

Guide Arm

Material - Housing

Mounting Style

Number of Conductors

Number of Receptacles

Packaging Type

Primary Cord/Cable Entry

Retraction Weight

Wire Size AWG

Ratchet Lock

10.67m (35.0')

Ratchet

5° increments over 270° Arc

Cast Aluminum

Rigid

3

2

Carton

1" NPT

1.8kg (4.0 lb)

12

Electrical

Bulb Included

Cord Type

Current - Maximum per Contact

GFCI

Lamp Type

Lamp Wattage - Maximum

On/Off Switch

Voltage - Maximum

N/A

14/3 SOOW

18.0A

No

N/A

N/A

N/A

120V

Material Info

Engineering Number

9385-3080



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130083 Series

This document was generated on 05/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300830280](#)