

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300830775

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead POW-R-MITE Industrial Duty Cable Reel, 16/3 SOW, 15.24m (50.0') Cord Length with 13W Fluorescent Hand Lamp and Ball Stop

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E22769

General

Product Family

Series

Cable Length

Comments

Depth

Duty

Enclosure Rating

Height

NEMA Configuration

Overview

Product Name

Type

UPC

Width

Electric Reels

130083

N/A

Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.

0.34m (13.50")

Industrial

NEMA 4

0.37m (14.50")

N/A

Reels - Woodhead

POW-R-MITE

Cable Reel

78678834642

244.35mm (9.620")

Physical

Cable Movement

Cord Length

Drum Lock

Guide Arm

Material - Coating

Material - Housing

Mounting Style

Number of Conductors

Packaging Type

Primary Cord/Cable Entry

Retraction Weight

Wire Size AWG

Ratchet Lock

15.24m (50.0')

Ratchet

5° increments over 270° Arc

Powder Coating

Cast Aluminum

Rigid

3

Carton

1" NPT

1.8kg (4.0 lb)

16

Electrical

Bulb Included

Cord Type

Current - Maximum per Contact

GFCI

Lamp Type

Lamp Wattage - Maximum

On/Off Switch

Voltage - Maximum

Yes

16/3 SOW

9.0A

No

Fluorescent

13W

Yes

120V

Material Info

Engineering Number

9228-86



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130083 Series

This document was generated on 07/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300830775