

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300830784

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead POW-R-MITE Industrial Duty Cable Reel, 12/3 SOW, 15.24m (50.0') Cord Length with 15A Pendant Outlet Box and Ball Stop

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR29921
General	
Product Family	Electric Reels
Series	130083
Cable Length	N/A
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Depth	0.34m (13.50")
Duty	Industrial
Enclosure Rating	NEMA 4
Height	0.37m (14.50")
NEMA Configuration	NEMA 5-15
Overview	Reels - Woodhead
Product Name	POW-R-MITE
Type	Cable Reel
UPC	78678833818
Width	244.35mm (9.620")
Physical	
Cable Movement	Ratchet Lock
Cord Length	15.24m (50.0')
Drum Lock	Ratchet
Guide Arm	5° increments over 270° Arc
Material - Coating	Powder Coating
Material - Housing	Cast Aluminum
Mounting Style	Rigid
Number of Conductors	3
Number of Receptacles	4
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Wire Size AWG	12
Electrical	
Bulb Included	N/A
Cord Type	12/3 SOW
Current - Maximum per Contact	18.0A
GFCI	No
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	120V
Material Info	
Engineering Number	92433-3000



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Relevant	
REACH SVHC	
Not Relevant	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

130083 Series

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300830784](#) [92433](#)