

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300850025

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead POW-R-MATIC Heavy Duty Cable Reel with Retraction Weight of 7lbs., 10/6 SOW, 25.91m (85.0') Cord Length with Flying Leads

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR29921

General

Product Family

Series

Cable Length

Comments

Depth

Duty

Enclosure Rating

Height

NEMA Configuration

Overview

Product Name

Type

UPC

Width

Electric Reels

130085

N/A

Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.

0.58m (22.750")

Heavy

NEMA 3R

0.59m (23.38")

N/A

Reels - Woodhead

POW-R-MATIC

Cable Reel

78678807520

577.90mm (22.75")

Physical

Cable Movement

Cord Length

Drum Lock

Guide Arm

Material - Coating

Material - Housing

Mounting Style

Number of Conductors

Packaging Type

Primary Cord/Cable Entry

Retraction Weight

Wire Size AWG

Ratchet Lock

25.91m (85.0')

Ratchet

Option Available

Powder Coating

Steel

Rigid

6

Carton

1" NPT

3.2kg (7.0 lb)

10

Electrical

Bulb Included

Cord Type

Current - Maximum per Contact

GFCI

Lamp Type

Lamp Wattage - Maximum

On/Off Switch

Voltage - Maximum

N/A

10/6 SOW

14.0A

No

N/A

N/A

N/A

600V

Material Info

Engineering Number

92764



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130085 Series

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300850025