

6

5

4

3

2

1


E

D

C

B


A



50 FT. OF #12-12 SOW CORD

0.563" DIA. REF.
MOUNTING HOLES
4-PLACES11.25/285.8 REF
MOUNTING LOCATION

14.5/368.3 REF





SPECIFICATIONS:
ELECTRICAL RATING: 10A, 600V
LIFT APPLICATION WITHOUT RATCHET
AGENCY APPROVAL: C.S.A.
NOTE: ROLLER GUIDE AND PIVOT BASE NOT INCLUDED.

RELEASE SALES DRAWING	EC NO: ICG2013-1990	DRWN: HRUIZ01	2013/06/21
	CHKD: HKNEELAN	APPR: JFMURPHY	2013/08/10
A	REV		

QUALITY SYMBOLS
$\nabla=0$
$\nabla C=0$

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±.005
2 PLACES	±.13	±.010
1 PLACE	±.25	±.020
ANGULAR ±1/2°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE INCH/MM	
DRAWN BY	DATE
HRUIZ01	2013/06/21
CHECKED BY	DATE
HKNEELAN	2013/06/21
APPROVED BY	DATE
JFMURPHY	2013/08/10
MATERIAL NO.	1300851070
SIZE	A

SCALE NTS	DESIGN UNITS INCH		THIRD ANGLE PROJECTION
TITLE			
125305312G5 CABLE REEL W/ 50 FEET OF #12-12 SOW CORD			
	MOLEX INCORPORATED		
DOCUMENT NO.			SHEET NO.
SD-130085-009			1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

6

5

4

3

2

1

E

D

C

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300851070