

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300870095

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead Super-Safeway Heavy Duty Hand Wind Reel with 3 Conductor Slip Ring, 12/3 SOW, 15.24m (50.0') Cord Length

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E19795

General

Product Family

Series

Cable Length

Comments

Depth

Duty

Enclosure Rating

Height

NEMA Configuration

Overview

Product Name

Type

UPC

Width

Electric Reels

130087

N/A

Hand Wind Reels are design for heavy duty industrial storage applications

0.34m (13.25")

Industrial

NEMA 1

0.45m (17.6")

NEMA 5-15

Reels - Woodhead

Super-Safeway

Hand Wind Reel

78678800872

241.30mm (9.500")

Physical

Cable Movement

Cord Length

Drum Lock

Material - Coating

Material - Housing

Mounting Style

Number of Conductors

Number of Receptacles

Packaging Type

Primary Cord/Cable Entry

Retraction Weight

Wire Size AWG

Manual

15.24m (50.0')

None

Powder Coating

Steel

N/A

3

1

Carton

N/A

N/A

12

Electrical

Bulb Included

Cord Type

Current - Maximum per Contact

GFCI

Lamp Type

Lamp Wattage - Maximum

On/Off Switch

Voltage - Maximum

N/A

12/3 SOW

15.0A

No

N/A

N/A

N/A

120V

Material Info

Engineering Number

932B123



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

China RoHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130087 Series

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300870095