

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300870097

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead Super-Safeway Heavy Duty Hand Wind Reel with 3 Conductor Slip Ring, 12/3 SOW, 30.48m (100.0') Cord Length

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E19795
General	
Product Family	Electric Reels
Series	130087
Cable Length	N/A
Comments	Hand Wind Reels are design for heavy duty industrial storage applications
Depth	0.34m (13.25")
Duty	Industrial
Enclosure Rating	NEMA 1
Height	0.45m (17.6")
NEMA Configuration	NEMA 5-15
Overview	Reels - Woodhead
Product Name	Super-Safeway
Type	Hand Wind Reel
UPC	78678800876
Width	241.30mm (9.500")
Physical	
Cable Movement	Manual
Cord Length	30.48m (100.0')
Drum Lock	None
Material - Coating	Powder Coating
Material - Housing	Steel
Mounting Style	N/A
Number of Conductors	3
Number of Receptacles	1
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	N/A
Wire Size AWG	12
Electrical	
Bulb Included	N/A
Cord Type	12/3 SOW
Current - Maximum per Contact	15.0A
GFCI	No
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	120V
Material Info	
Engineering Number	932D123



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130087 Series

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300870097](#)