

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300900008

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead Standard Cord Reel, 16/3 SJTOW Cord, 10.67m (35.0') Cord Length with 15A Connector, NEMA 5-15

Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E22769
General	
Product Family	Electric Reels
Series	130090
Cable Length	0.457m (1.50')
Comments	Ratchet Lock (ON/OFF Switchable)
Depth	0.24m (9.59")
Duty	Standard
Enclosure Rating	NEMA 1
Height	0.32 (12.62")
NEMA Configuration	NEMA 5-15
Overview	Reels - Woodhead
Product Name	Super-Safeway
Type	Cord Reel
UPC	78678835149
Width	13.06mm (5.160")
Physical	
Cable Movement	Ratchet Lock
Cord Length	10.67m (35.0')
Drum Lock	Ratchet
Material - Coating	Powder Coating
Material - Housing	Steel
Mounting Style	Swinging
Number of Conductors	3
Number of Receptacles	1
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	0.9kg (2.0 lb)
Wire Size AWG	16
Electrical	
Bulb Included	N/A
Cord Type	16/3 SJTOW
Current - Maximum per Contact	6.0A
GFCI	No
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	No
Voltage - Maximum	120V
Material Info	
Engineering Number	945-1547



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130090 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300900008