

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300900010](#)
Status: **Active**
Overview: [Reels - Woodhead](#)
Description: Woodhead Standard Duty Reel, 16/3 SJTOW Cord, 10.67m (35.0') Cord Length with 13W Fluorescent Hand Lamp and Handle Ballast

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E22769

General

Product Family Electric Reels
Series [130090](#)
Cable Length 0.457m (1.50')
Comments Ratchet Lock (ON/OFF Switchable)
Depth 0.24m (9.59")
Duty Standard
Enclosure Rating NEMA 1
Height 0.32 (12.62")
NEMA Configuration NEMA 5-15
Overview [Reels - Woodhead](#)
Product Name Super-Safeway
Type Cord Reel
UPC 78678827906
Width 13.06mm (5.160")

Physical

Cable Movement Ratchet Lock
Cord Length 10.67m (35.0')
Drum Lock Ratchet
Material - Coating Powder Coating
Material - Housing Steel
Mounting Style Swinging
Number of Conductors 3
Packaging Type Carton
Primary Cord/Cable Entry N/A
Retraction Weight 0.9kg (2.0 lb)
Wire Size AWG 16

Electrical

Bulb Included Yes
Cord Type 16/3 SJTOW
Current - Maximum per Contact 6.0A
GFCI No
Lamp Type Fluorescent
Lamp Wattage - Maximum 13W
On/Off Switch Yes
Voltage - Maximum 120V

Material Info

Engineering Number 945-3-86



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130090](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300900010