

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300900019

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead Standard Cord Reel, 16/3 SJTOW Cord, 10.67m (35.0') Cord Length with 15A Pendant Outlet Box, Two Duplex, NEMA 5-15 Outlets

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E22769
General	
Product Family	Electric Reels
Series	130090
Cable Length	0.457m (1.50')
Comments	Ratchet Lock (ON/OFF Switchable). (2) NEMA 5-15 Duplex Receptacles
Depth	0.24m (9.59")
Duty	Standard
Enclosure Rating	NEMA 1
Height	0.32 (12.62")
NEMA Configuration	NEMA 5-15
Overview	Reels - Woodhead
Product Name	Super-Safeway
Type	Cord Reel
UPC	78678875261
Width	13.06mm (5.160")
Physical	
Cable Movement	Ratchet Lock
Cord Length	10.67m (35.0')
Drum Lock	Ratchet
Material - Coating	Powder Coating
Material - Housing	Steel
Mounting Style	Swinging
Number of Conductors	3
Number of Receptacles	4
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	0.9kg (2.0 lb)
Wire Size AWG	16
Electrical	
Bulb Included	N/A
Cord Type	16/3 SJTOW
Current - Maximum per Contact	6.0A
GFCI	No
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	No
Voltage - Maximum	120V
Material Info	
Engineering Number	966



EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130090 Series

This document was generated on 07/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300900019